## J2400 Series Benchtop Dispensing Robot

Activators

Anaerobics Cyanoacrylates

Silicones Solvents

**Primers UV-cure** 



Even complex program patterns can be developed quickly using the simple point to point teach pendant. Dispense adhesive direct from syringes or optional metering valves and pressure pots. With fast indexing speeds, high accuracy and simple programming; robots are an ideal solution for most dispensing applications in a 400mm x 400mm work area. 3 or 4 axis versions available. Recommended optional light guard safety cages also available.

> Adhesive Dispensing Ltd Solutions customers stick with...

The JR2400 series robots are designed to apply rapid dots, beads, arcs, circle and potting deposits to products placed on the base plate. The overhead gantry indexes into position to make the required deposit without mess, waste or guesswork.

The robots are programmed via the LCD electronic teach pendant, or using optional windows based software on a PC. The robust robots will dispense most assembly fluids including epoxies, PU's, glues, CA's, silicones, greases, adhesives, inks, gels, primers and activators.

Each robot is supplied with a teach pendant, CE start/ stop box, digital controller or solenoid valve, syringe barrel mount bracket, component kit. Easy to mount valves or sealant cartridge retainers.



## **Features**


Dispense liquids and pastes in dots, lines, or arcs Repeatability of +/- 0.01 mm Powerful on-board 32 bit processor Safe operation via area sensor and interlock capability Easy to program via teach pendant or optional software Continuous path motion for perfect dispensing Storage of up to 255 programs or 6000 points 400mm x 400mm x 150mm work area CE certified and 1 Year warranty

## **Dispense Robots**

## **Adhesive Dispensing Ltd**

Solutions customers stick with...

Model number		JR2403N	JR2404N	
Axis-type <sup>**1</sup>		3	4	
	X,Y axis		400mm>	<400mm
Range of operation	Z axis		150	mm
	R axis			±360°
	Work		11	kg
Portable weight *2	Tool		64	g
	PTP(X,Y)		800mm/sec(8~	-800mm/sec)**
Speed	PTP(Z)		320mm/sec(3.2-	~320mm/sec)**
	PTP(R)			800°/sec (8~800°/sec)**
	CP (X,Y,	Z) **3	800mm/sec(0.1-	
Acceptable Moment of Inertia		tia		90Kg·cm²
	X,Y axis		±0.0	lmm
Repeatability accuracy	Z axis		±0.0	lmm
	R axis			±0.02°
Dimensions	Width×Depth×Height		590mm×630	mm×800mm
Weight		42	kg	
Power source		•	AC	
Consumption current				
Working ambient temperature				
Relative humidity				
Teaching Method			Remote	
Teaching System · Sin		C-Points:Simple or broad-use teaching systems mple: Easy teaching just by registering position and paramet road-use: User-oriented programming such as I/O control, tea		
Teaching Pattern		<ul> <li>Programming by teaching pendant (Optional)</li> <li>Off line teaching using a PC (Optional)</li> </ul>		
Program capacity				
Data memory capacity				
Drive method				
Control method				
Interpolate Function			3	
External interface			RS232C 1ch(Fo	r PC)、2ch(For E
External input/output				IN
PLC function				





Power source	AC90~132V/AC180~250V (single phase)				
Consumption current	200VA				
Working ambient temperature	0∼40℃				
Relative humidity	20~95% (no condensation)				
Teaching Method	Remote Teaching (JOG), Manual Data Input (MID)				
Teaching System	JR C-Points:Simple or broad-use teaching systems · Simple: Easy teaching just by registering position and parameter · Broad-use: User-oriented programming such as I/O control, teaching by point job.				
Teaching Pattern	<ul> <li>Programming by teaching pendant (Optional)</li> <li>Off line teaching using a PC (Optional)</li> </ul>				
Program capacity	255programs				
Data memory capacity	Maximum 30,000 points <sup>*5</sup>				
Drive method	5-phase stepping motor				
Control method	PTP and CP				
Interpolate Function	3dimension line and Arc interpolation				
External interface	RS232C 1ch (For PC)、2ch (For External Device-optional) / RS422 1ch (For Teaching Pendant only)				
External input/output	IN : 16,OUT : 16 (IN : 24,OUT : 24 Optional)				
PLC function	100programs,1000steps/1program				

B You E